ACTIVATED CARBON LAYER IS INCORPORATED TO REMOVE NUISANCE ODOURS

TECHNICAL **SPECIFICATION**

RESPIRATORY PROTECTION

INSTRUCTIONS FOR USE

Mask must be fitted in accordance with the instructions supplied

Care must be taken to ensure that the correct mask type is selected for the work to be carried out

If in doubt as to the type of mask required seek professional guidance

PERFORMANCE

Springfit[™] 421 and 425 offer an assigned protection factor (APF) of 10 x Workplace Exposure Limit (WEL) for fine dusts, fibres, fumes,

Springfit™ 431, 435 and 436 offer an APF of 20 x WEL for fine dusts, fibres, fumes, and mists

Respiratory protection is only effective if it is correctly selected, fitted and worn throughout the time when the wearer is exposed to respiratory contaminants

SPRINGFIT™ OPTIONS

| Springfit™ Model | EN 149 Classification | Typhoon™ Valve | Carbon Filter |
|---------------------|--------------------------|-------------------|------------------|
| 421 | FFP2 NR D | No | No |
| 425 | FFP2 NR D | Yes | No |
| 431 | FFP3 NR D | No | No |
| 435 | FFP3 NR D | Yes | No |
| 436 | FFP3 NR D | Yes | Yes |

CLEANING & MAINTENANCE

Not applicable - disposable product


Store the masks out of sunlight away from chemicals in a dry atmosphere

MAN MADE FIBRES:

The mask has an ergonomic 3D design to fit most face shapes



POLYPROYLENE INNER SKELETON:





SPRINGFIT™ FEATURES

Face Seal: Improved face seal for added comfort

Typhoon™ Valve: Optional Modern design valve allows for lower breathing resistance

Carbon Filter: The Springfit™436 has an integrated Carbon filter to help reduce nuisance odours

CONFORMITY & MARKINGS

Meets the FFP2 and FFP3 requirements of EN149 (as applicable)

EU Type Examination Certificate Number 682743

EN149:2001 + A1:2009

DISCLAIMER: Information presented within this technical specification was correct on date of issue. Information may be subject to change without notice as part of ongoing product improvement and development. To confirm any specific piece of information shown is current please email technical@jspsafety.com .






















SPRINGFIT* 400 SERIES ACTIVATED CARBON LAYER IS INCORPORATED TO REMOVE NUISANCE ODOURS

TECHNICAL SPECIFICATION

RESPIRATORY PROTECTION


SPRINGFIT ™ 421, 431 DIMENSIONS OF INNER PACKAGING

Box Quantity: 10



SPRINGFIT ™ 421, 431 DIMENSIONS OF OUTER PACKAGING

Box Quantity: 100



LIMITATIONS OF USE

Protection will only be offered if the mask is fitted correctly

The mask, when in contact with the skin may cause allergic reactions to susceptible individuals

If this occurs leave the hazard area, remove mask and seek medical advice

The use by date is printed on the outer packaging

Do not use where exposure to chemical gases may be experienced

Use in well ventillated areas only, which are not deficient in oxygen and do not contain explosive atmospheres

Ensure good seal around the face is created before entering the hazard area


The working life of the mask is nominally one day (this is based on an working day shift of 8 hours), however it may be affected by many factors, including work rate, airflow and concentration of any contaminent in the atmosphere. The mask should be changed immediately if,

- a.) Breathing difficulties due to clogging are experienced,
- b.) Breakthrough of a contaminent is detected by smell, taste or any other means, or
- c.) The mask becomes damaged

This mask is not designed to be worn by people with facial hair


SPRINGFIT™ 425, 435, 436 DIMENSIONS OF INNER PACKAGING

Box Quantity: 10



SPRINGFIT™ 425, 435, 436 DIMENSIONS OF OUTER PACKAGING

Box Quantity: 100



DIMENSIONS OF SPRINGFIT™ 421, 431

Depth: 60mm

Width: 210mm

Height: 125mm

Weight: 13.5g (Approx)

DIMENSIONS OF SPRINGFIT™ 425, 435, 436

Depth: 70mm

Width: 210mm

Height: 125mm

Weight: 18.8g (Approx)



DISCLAIMER: Information presented within this technical specification was correct on date of issue. Information may be subject to change without notice as part of ongoing product improvement and development. To confirm any specific piece of information shown is current please email technical@jspsafety.com .













